

UTILCO Heavy Wall Heat Shrink



TYPE HSHW

Features

- 3:1 shrink ratio
- UL Listed 486D and CSA Certified for 600 volts
- Inner adhesive liner
- Flame retardant
- 24999-B12 contains 3 ea. 24005, 24006, 24008, 24009

Benefits

- Provides a wide range of coverage when used on connectors and cable
- Ensures reliability for insulating terminations and splices
- Melts to form intimate contact with part to seal out elements and produce a watertight seal suitable for above ground, direct burial and underwater applications
- Meets Mil Spec 23053/15 rigid requirements for flame retardancy



Catalog Number	Wire Size	Quantity Per Package	Exp. Id.	Rec. Id.	Recovered Wall Thickness	Length
21106-B3*	6-14	3	0.400	0.150	0.060	6"
21112-B3*	6-14	3	0.400	0.150	0.060	12"
21206-B3	1-8	3	0.750	0.220	0.090	6"
21209-B3	1-8	3	0.750	0.220	0.090	9"
21212-B3	1-8	3	0.750	0.220	0.090	12"
21230	1-8	-	0.750	0.220	0.090	30"
21406-B2	4/0-2	2	1.100	0.375	0.120	6"
21409-B2	4/0-2	2	1.100	0.375	0.120	9"
21412-B2	4/0-2	2	1.100	0.375	0.120	12"
21448	4/0-2	-	1.100	0.375	0.120	48"
21609-B2	400kcmil-4/0	2	1.500	0.500	0.140	9"
21612-B2	400kcmil-4/0	2	1.500	0.500	0.140	12"
21648	400kcmil-4/0	-	1.500	0.500	0.140	48"
21709-B	1000kcmil-500kcmil	1	2.000	0.750	0.155	9"
21712-B	1000kcmil-500kcmil	1	2.000	0.750	0.155	12"
21748	1000kcmil-500kcmil	-	2.000	0.750	0.155	48"

*UL Listed wire range 12 - 6.

UL File E158587