



S28789

15.5A19/LED/27K/ND/120V/4PK
 15.5 watt; A19 LED; 2700K; Medium base; 220' beam spread; 120 volts; 4-pack

Features

- A-Shaped replacement lamp
- 100w equivalent
- Approved for enclosed fixtures
- Damp location rated



S28789

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S28789	045923287893	120	15.5	100W	0.91	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	15.5A19/LED/27K/ND/120V/4PK	Non-Dimmable	Frosted	5-1/2"	2-5/8"	1600	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80	220	-25C (-13F) to a maximum of +45C (+113F)	12-4pks	Box	ENERGY STAR
CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty			
Non-Compliant Possible sub: S8566	Yes	Yes	cULus - Damp Location Rated	3 Year Limited - 10 hour use per day			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

