

# YDS29

by Burndy  
Catalog ID: YDS29

Prop65

Hysplice, 250 (7, 19, 37) Str. , 7-1/2 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U169 Die, (9), Y45 Tool, U169 Die With PT-6515 Adapter, (9), Y46 Tool, U169 Die With PUADP-1 Adapter, (9), Y48B Tool, C169 Die, (3), Y60BHU Tool, L169 Die, (3), Die Index: 169 Element A, Conductor Type: Stranded Copper



## Product Details

### General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	169
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810014646

### Dimensions

Dimension - B Length fraction	3-1/2 in
Dimension - B Length inch	3.54 in
Dimension - L Length Overall mm	190 mm
Dimension - Length Overall inch	7.47 in
Dimension - Outside Diameter inch	0.95 in

### Conductor Related

Conductor - Copper Str Size	250 kcmil
-----------------------------	-----------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)