



# S2260

80PAR38/HAL /XEN /FL /2PK /120V  
 80 watt; Halogen; PAR38; Clear; 1500 Average rated Hours;  
 1600 Lumens; Medium Skirted base; 120 volts; 2-Pack

### Features

- Energy Saving Halogen
- Bright, Crisp light
- Indoor / Outdoor
- Uniform light output



S2260

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S2260	045923022609	80	120	PAR38	Medium Skirted	E26SK	80PAR38/HAL /XEN /FL /2PK /120V
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Clear	5-5/16"	4-3/4"	CC-8	1600	3050	Neutral White	1500
Pack	Package Type	Beam Spread Deg	CBCP	Dimmable/Non-Dimmable	RoHS Compliant		
8	Box	30	2560	Dimmable	Yes		



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027

