



BURNDY Catalog Number YA25L2BOX
 UPC Number 781810313251
 Description CULUG-1/0 STR-SHORT-1/4"
 Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Strip Length	15/16
Length (in)	1.84
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.88
Pad Width (in)	0.75
General	
Number of Holes	1
Product Description	Cu Comp Terminal code Cond, Bvl Entry, 1 Hole/W/InspWindow, 1/0 AWG Code, 100 Navy, 600 V-35 kV, 1/4" Stud, Std bbl, Tin Plated, Pink, 12 or 348 Index
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	1/0
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
 47, industrial Park Drive
 Manchester NH03109

BURNDY Technical Servcies
 47, industrial Park Drive
 Manchester NH03109

Hours: 8.00 AM - 5.00 PM
 Monday - Friday
 Phone: 000-346-4175

