



S9405

7PAR20/LED/40'/2700K/120V/D
 7 watt PAR20 LED; 2700K; 40' beam spread; Medium base;
 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9405

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9405	045923094057	120	7	50W	PAR20	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
7PAR20/LED/40'/2700K/120V/D	Dimmable	Compatible dimmers for S9405	Silver	3-1/32"	2.50"	525	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	40	24/6	Box	ENERGY STAR	Yes

Fixture Type	UL or ETL Listed	UL Classification	Warranty
Enclosed Rated	Yes	cULus - Wet Location Rated	3 Year Limited



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

