



# S9400

7PAR20/LED/25'/2700K/120V/D  
 7 watt PAR20 LED; 2700K; 25' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- ABS Lens
- Dimmable



S9400

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9400	045923094002	120	7	50W	PAR20	Medium	E26

  

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
7PAR20/LED/25'/2700K/120V/D	Dimmable	<a href="#">Compatible dimmers for S9400</a>	Silver	3-1/32"	2.50"	525	25000

  

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	25	24/6	Box	ENERGY STAR	Yes

  

Fixture Type	UL or ETL Listed	UL Classification	Warranty
Enclosed Rated	Yes	cULus - Wet Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
 800.43.SATCO  
 (800.437.2826)  
 www.satco.com

Distribution Centers:  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

Corporate Offices:  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027

