



S9630

6.5R20/LED/2700K/525L/120V
 6.5watt; LED R20; 2700K; 107° beam spread; Medium base;
 120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9630

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9630	DiTTO	045923096303	120	6.5	50W	0.92	R20
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches
Medium	E26	6.5R20/LED/2700K/525L/120V	Dimmable	Compatible dimmers for S9630	Frosted	3-15/16"	2.50"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack
525	25000	2700	Warm White	80	107	-25C (-13F) to a maximum of +45C (+113F)	24/6
Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
Box	ENERGY STAR	Non-Compliant Possible sub: S9614	Yes	Yes	cULus - Damp Location Rated	5 Year Limited - 10 hour use per day	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

