



BURNDY Catalog Number	YA31A3
UPC Number	781810755808
Description	350 AL 2-HOLE 1/2
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Strip Length	2 1/8
Length (in)	6.07
Tongue Type	Standard
Bolt Hole Size (in)	0.52
Thickness	0.39
B Length (in)	1.85
Pad Width (in)	1.52
E - in	1.75
General	
Number of Holes	2
Product Description	Aluminum Compression Lug, 2 Hole w/o Inspection Window, 350 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Tin Plated
Conductor(s)	
Aluminum Size (Range)	350 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	350 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Brown
Plated (Yes or No)	Y
Index Number	299
Product Material	Aluminum
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA
47, industrial Park Drive
Manchester NH03109

BURNDY Technical Services
47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

