

# PATCUT245CUAL18V

by Burndy  
Catalog ID: PATCUT245CUAL18V

Prop65

Battery Actuated Cutting Tool, Hydraulic Self Contained, 2.45" O.D Cu & Al, 18V Ni-MH, with 120V Charger.

- 180° head rotation
- Cuts up to 2.45" diameter copper/aluminum cable
- Specialized latch style cutting head for interference-free closure for mid-span work
- Ergonomic design, overmolded handle

Features: Battery powered cutting technology, Easy tool operation and portability, Advance design high-speed pump completes tough cuts faster, Longer life, efficiency, and reliability, Specialized latch head design, Interference free closure for mid-span cuts, Ergonomic design allows one hand operation, User has one hand free to manipulate material to be cut, 180-degree head rotation, Versatile head positioning allows user to get into tight areas easier, Mechanical ram release, Reliable ram release (no battery power consumption), Operates on 18-volt Ni/MH batteries, Eliminates voltage depression or memory issues, Durable high impact formed carrying case, Provides tool protection and stores all accessories, 5-year limited warranty on tool (excluding blades) and 1-year on batteries and charger, Customer satisfaction and support 5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



## Product Details

### General

Application	For Use On: Copper & Aluminum Cable: Up to 2.45 O.D. For Copper and Aluminum cable only. Do not cut steel, ground rods, rebar, or guy wire.
Battery Type	Nickel Metal Hydride (NiMH)
Crimp Force Capacity	6 ton
Recharge Time	0.75 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutting Tool
Trade Name	PATRIOT®
Type	Cutters
UPC	781810412473
UPC 12 Digit	7818104124733

### Dimensions

Height	14.75 in
Length	18 in
Weight	14.5 lb
Width	3.75 in

### Electrical Ratings

Operating Voltage	18 V-DC V
-------------------	-----------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)