



# S8790

16A21/LED/50K/ND/120V/4PK  
 16 watt; A21 LED; 5000K; Medium base; 220' beam spread;120 volts; 4-pack

## Features

- A-Shaped replacement lamp
- 100w equivalent
- Approved for enclosed fixtures
- Damp location rated



S8790

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S8790	045923087905	120	16	100W	0.94	A21	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	16A21/LED/50K/ND/120V/4PK	Non-Dimmable	Frosted	5-1/2"	2-5/8"	1600	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
5000	Natural Light	80	220	-20C (-4F) to a maximum of +45C (+113F)	12-4pks	Box	ENERGY STAR
RoHS Compliant		UL or ETL Listed		UL Classification		Warranty	
Yes		Yes		cULus - Damp Location Rated		<a href="#">3 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

