



## PATCUT245LI

by Burndy  
Catalog ID: PATCUT245LI

Prop65

Battery Cutter Tool, with 120V Charger, 12 Ton, 2.45" O.D Cu & Al, 18V Lithium Ion.

- 180° head rotation
- Cuts up to 2.45" diameter copper/aluminum cable
- Specialized latch style cutting head for interference-free closure for mid-span work
- Ergonomic design, overmolded handle

Features: Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics for ultimate reliability in the harshest environments, Overmolded handle for comfort and improved grip, allows for one-handed operation for advance, retract, and hold, Specialized latch head design for interference free closure for mid-span cuts, 18-volt Lithium-Ion batteries provide 2.5 times more charge/discharge cycles than traditional Ni-Cd batteries and provide 430 percentage more lifetime work, 30 minute charger controls current, voltage and temperature to maximize battery life, Forced air cooling fan cools the battery by forcing cool air through the battery's built-in air vents, 180 DEG head rotation allows user to get into tight areas easier, Ergonomically balanced tool design eases operation and lessens fatigue, Durable high impact formed carrying case provides superior protection and stores all accessories, 5-year limited warranty on tool (excluding blades), Lifetime warranty on INFINITY DRIVE, 1-year warranty on batteries and charger 5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE

## Product Details

### General

Application	For Use On: Copper & Aluminum Cable: Up to 2.45 O.D. For Copper and Aluminum cable only. Do not cut steel, ground rods, rebar, or guy wire.
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutting Tool
Trade Name	PATRIOT®
Type	Cutters
UPC	781810505243
UPC 12 Digit	7818105052433

### Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18V DC
-------------------	--------

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)