



## PATCUT129LI

by Burndy  
Catalog ID: PATCUT129LI

Prop65

Battery powered crimping tool, 14.5 in L, 3.5 in W, 18 V-DC.

- Special Latch head design provides interference free closure for Mid-Span cuts
- 180° head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold
- Durable high impact carrying case

Length: 14.5 IN, Width: 3.5 IN, Height: 13.5 IN, Operating Voltage: 18 VDC, Recharge Time: 30 MINT, Accessories: PATCHGR-LI 120 VAC Charger, PT208620 Lanyard, BAT18VLI Replacement Battery, Battery Type: Li-Ion, Operating Pressure: 10000 PSI, Covered Head: No, Number Of Conductors Accomodated (max): Ground Rod Up To 5/8 IN, EHS Guy Strand Up To 3/8 IN, Soft Steel Bolts Up To 5/8 IN, Rebar Up To 1/2 IN, Aluminum - 1.29 IN Diameter, Standard Guy Strand Up To 1/2 IN, Copper - 1.29 IN Diameter, Weight: 10.2 LB5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE®

## Product Details

### General

|                      |   |
|----------------------|---|
| Application          | The PATCUT129-LI is capable of cutting up to 1.29 IN diameter copper and aluminium cable, 1113 ACSR, 5/8 IN ground rods, ½ IN rebar, 5/8 IN diameter soft steel bolts up to ½ IN standard guy strand and up to 3/8 IN EHS guy strand. |
| Battery Type         | 3.0 Ah Li-Ion   |
| Crimp Force Capacity | 7 ton   |
| Die Type             | Dieless   |
| Item Type            | 3A  |
| Recharge Time        | 0.5 h   |
| Sub Brand            | PATRIOT® CUTTER   |
| Tool Type            | Battery Actuated Cutting Tool   |
| Trade Name           | PATRIOT®  |
| Type                 | Cutters   |
| UPC                  | 781810505212  |
| UPC 12 Digit         | 7818105052122   |

### Dimensions

|        |         |
|--------|---------|
| Height | 13.5 in |
| Length | 14.5 in |
| Weight | 10.2 lb |
| Width  | 3.5 in  |

### Electrical Ratings

|                   |        |
|-------------------|--------|
| Operating Voltage | 18V DC |
|-------------------|--------|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)