



**BURNDY Catalog Number**  
**UPC Number**

PATMD6LI  
7818105288600  
BATTERY ACTUATED CRIMPER W/  
D3/BG GROOVE  
Active

**Description**  
**Status**

**Web Use**  
BURNDY Product Line

**Dimensional**

Width (in) 2.8  
Length (in) 21.3  
Height (in) 4.25

**General**

Weight lbs 7.5  
Warranty 5-year limited warranty; 1 year on battery and charger;  
Lifetime on INFINITY DRIVE®;  
Battery Actuated Crimping Tool, Hydraulic Self Contained, 6  
Ton Output Force, 10 AWG(Sol)-500 kcmil Copper, 14  
Product Description AWG(Sol)-350 kcmil Aluminium, 14 AWG(Sol)-4/0 ACSR, W  
and X Dies, 18V Lithium Ion

**Approvals / Certifications**

ROHS Exempt  
Compatible  
CULUS N

**Physical**

Pressure (Operating) 7800  
Crimp Force 6 tons (5.4 metric tons)  
Force 6 tons  
Developed  
Operating Voltage 18 Volt Lithium-ion

**Documentation**

Literature • [/burndy/documentation/2011\\_burndy\\_tooling\\_catalog](/burndy/documentation/2011_burndy_tooling_catalog)

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175