



## YAV6CL2TC14FX90

by Burndy  
Catalog ID: YAV6CL2TC14FX90

Prop65

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, #6 Weld, 6(61/#24)DLO Flex, #6 AWG Code, 30 Navy, 600 V-35 kV, 1/4" Stud, 0.63" Spacing, 90 Deg Bent, Std bbl.

Two hole, Copper compression terminal flex conductor, standard barrel

## Product Details

### General

Application	For Flex Conductors
Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	<ul style="list-style-type: none"> <li>Chamfered</li> <li>Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810033975
UPC 12 Digit	7818100339755

### Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.52 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	9/16 in

Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	6 (61/24) DLO
Conductor - Copper DLO Size Range	6 (61/24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	30 Navy
Conductor - Copper Str Navy Size Range	30 Navy
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - CopperWeld Str Size	#6 WELD (61/24)
Conductor - CopperWeld Str Size Range	#6 WELD (61/24)
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)