
Heavy Duty Grade Vinyl Plugs & Connectors

2-Pole, 3-Wire Grounding 15A, 125V/AC 20A, 125V/AC



Features

- Solid brass plug blades are firmly embedded in body
- Vinyl plugs and connectors resist chemical attack
 and are less brittle in extremely low temperatures
- Vinyl angle plugs have eight possible positions for maximum convenience
- Terminals in individual chambers to positively insulate conductors
- Terminal screw clamps are designed to contain wire and prevent binding
- Combination Slot/Phillips head mounting and terminal screws for installation flexibility (Slot/ Robertson screws in Canada where available)



4867ANW

4229

· Terminal screws backed out and ready for wiring

Vinyl Plugs & Connectors 📵 🚯 🏧								
R A	ating V/AC	Description	Cord Diameter	Color	Plug Catalog No.	Connector Catalog No.	٩	
15	125	NEMA 5-15, Straight Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4867	□ 4887	•	
		NEMA 5-15, Angled Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4867AN		•	
		NEMA 5-15, Angled Body	0.25-0.66" (6.4-16.6mm)	W	□ 4867ANW		•	
20	125	NEMA 5-20, Straight Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4409	□ 4228	•	

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified except 4228

Vinyl Plugs & Connectors) <u>NOM</u> 426				
R A	ating V/AC	Description	Cord Diameter	Color	Plug Catalog No.	Connector Catalog No.	٩
		NEMA 5-20, Angled Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4409AN		•

Listed to UL498, file no. E15012; NOM certified except 4228

Vinyl Plugs & Connectors 🛛 🕀 🎬

Rating					Plug	Connector	
Α	V/AC	Description	Cord Diameter	Color	Catalog No.	Catalog No.	
15	250	NEMA 6-15, Straight Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4866	□ 4227	٠
		NEMA 6-15, Angled Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4866AN		٠
20	250	NEMA 6-20, Straight Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4509	□ 4229	•
		NEMA 6-20, Angled Body	0.25-0.66" (6.4-16.6mm)	Y	□ 4509AN		•

Listed to UL498, file no. E15012; CSA certified to C22.2, no. 42; NOM certified except 4227 & 4229

Color Ordering Information:

Y (Yellow), W (White)



Dimensional Information: B-70 Specification Information: Please visit www.cooperwiringdevices.com. Specifications and availability are subject to change without notice.

NAFTA Compliant - see page F-21

