



Pigtail Lampholders

Medium and
Miniature Base
75W 125V
660W 250V
660W 600V

Pigtail Lampholders

FEATURES


- For use in electrical equipment, harnesses, light strings and related applications.
- Wire leads are 5" (127mm) of color-coded stranded wire, stripped 1" (25.4mm) for easy connection.
- Rubber sockets have an extended lip to seal against bulb.
- Metal shell interiors are aluminum, 145 nickel-plated copper.
- 124 weatherproof socket has sealed leads where they enter husk.



145



722



306

Medium Base

Rating

W	V	Description	Wire Size	Catalog No.
660	600	Rubber	#14	145*
660	600	Rubber	#16	124
660	250	Phenolic	#14	722†

*cUL Listed
†CSA certified

Miniature Base

Rating

W	V	Description	Wire Size	Catalog No.
75	125	Phenolic	#20	306††

††Not NOM certified

R-7 Lampholders

TESTING & CODE COMPLIANCE

- UL Listed, file E7430, UL 496 requirements, Meet CSA requirements, C22.2 no. 43
- NOM Certified

MATERIAL CHARACTERISTICS

Temperature Rating:
-40°C to 65°C