

All load dimmers

Product description

Single-pole & multi-location
 600W/VA, 1000W/VA, 120V/AC
 Rated for all common lighting loads - Dimmable LED, Dimmable CFL, INC/HAL, ELV, MLV, FLR

Design features

- Electro-mechanical push pad for ON/OFF operation with separate DIM/BRIGHT bar (AAL06)
- 10-second delayed OFF feature (AAL06)
- LED light level display for presetting illumination levels and master/accessory units for multi-location control (AAL06)
- Adjustable low-end and high-end dimming range to prevent lamp flickering (AAL06)
- No de-rating required for CFL/LED in multi-gang installations (AAL06)
- No de-rating required in multi-gang installations (DAL06P, SAL06P, TAL06P1)
- Preset feature allows user to return to previous light level when turning lights ON (AAL06, DAL06P, SAL06P, TAL06P1)
- Adjustable low-end trim (AAL06, DAL06P, SAL06P, TAL06P1)
- Fully adjustable rapid start setting for optimal lamp start-up at low preset light levels (AAL06, DAL06P, TAL06P1)
- Each dimmer comes with color kit package which includes 3 colors (except SAL06P)
- Title 24 compliant



AAL06



DAL06P



SAL06P



TAL06P

Dimmer features	Smart AL dimmer (AAL06)	Decorator AL dimmer (DAL06P)	Slide AL dimmer (SAL06P)	Toggle AL dimmer (TAL06P1)
Rapid start feature	Selectable ON or OFF	Fully adjustable	Fixed ON	Fully adjustable
Adjustable high-end trim	•	—	—	—
Adjustable low-end trim	•	•	•	•
Wiring configurations	Single-pole or multi-location	Single-pole or 3-way	Single-pole or 3-way	Single-pole or 3-way
Color change kits	•	•	—	•

Rated for all common lighting loads

- Dimmable Compact Fluorescent (CFL)
- Dimmable Light-Emitting Diodes (LED)
- Electronic & Magnetic Low-Voltage (ELV)
- Incandescent/Halogen (INC/HAL)
- Fluorescent (FLR)

All load dimmers

Rating		Compatible lamp types	Description	Color suffix	Catalog no.	TITLE 24
W/AC	V/AC					
300	120	Dimmable LED/CFL	Smart dimmer master, single-pole/ multi-location with presets and LEDs, neutral required	C1, C2, C4, C5	<input type="checkbox"/> AAL06-__	•
600	120	INC, HAL, FLR, MLV, ELV				
300	120	Dimmable LED/CFL	Decorator dimmer, single-pole/ 3-way, preset	C1, C2, C4, C5	<input type="checkbox"/> DAL06P-__	•
600	120	INC, HAL, FLR, MLV, ELV				
300	120	Dimmable LED/CFL	Slide dimmer, single-pole/3-way with preset & LED indicator	A, BK, GY, LA, V, W	<input type="checkbox"/> SAL06P-__	•
600	120	INC, HAL, FLR, MLV, ELV				
300	120	Dimmable LED/CFL	Toggle dimmer, single-pole/ 3-way preset	C1, C2, C4, C5	<input type="checkbox"/> TAL06P1-__	•
600	120	INC, HAL, FLR, MLV, ELV				

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY)

A	BK	GY	LA	V	W
(Almond)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)
A	W	V	LA	W	V
C1 Color Kit			C2 Color Kit		
A (Almond), W (White), V (Ivory)			LA (Light Almond), W (White), V (Ivory)		
BK	W	V	BK	W	GY
C4 Color Kit			C5 Color Kit		
BK (Black), W (White), V (Ivory)			BK (Black), W (White), GY (Gray)		

Derating information: G-19 **Dimensional information:** A-42, A-43 **Specification information:** Please visit www.eaton.com/wiringdevices Mark 10® and AmbiStar® are registered trademarks of Philips Advance; Tu-VWire® is a registered trademark of Lutron.

Compliances, specifications and availability are subject to change without notice.

Indicates Title 24 compliant - Page G-4