

## LED accent lights

### LED combination nightlights

**Product description**

Single-pole  
1W 120V/AC, back & side wire

**LED accent lights features & benefits**

- Nightlight is dimmable to desired setting
- Nightlight is controlled by a photo sensor that turns on in the dark, off in light
- Easily disable photo sensor for Hi/Med/Low/Off settings
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper is used
- Convenient built-in wire strippers speed installation
- Backwire clamps on side terminals provide for easy installation of #12 and #14 AWG
- Thermoplastic top and back are virtually unbreakable to deliver years of durable performance
- Steel mounting strap is zinc plated for added corrosion resistance
- Ultrasonic welding and integrated construction of the strap and body provide superior ground integrity even under heavy use
- Tri-combo screw heads offer greater installation flexibility



7738




7737

**Combination LED wallbox nightlight w/switch & full nightlight** 

Rating		Description	Color suffix	Catalog no.
A	V/AC			
15	120	Single-pole switch with nightlight	A, BK, LA, V, W	□ 7738__
		Full nightlight	A, BK, LA, V, W	□ 7737__

**Color ordering information:**

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Black), BN (Brushed Nickel), LA (Light Almond), V (Ivory), W (White)



**Material characteristics:** Faceplate, die-cast aluminum. Back body, ABS plastic. Strap, aluminum. Wire, 18 AWG, 600V. Temperature rating: 25°C (77°F) **Specification information:** E-38

**Compliances, specifications and availability are subject to change without notice.**