



PRODUCT SEARCH



SUPP



DIST

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CONTACT](#)**FINISHING**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &](#)[Miscellaneous](#)**Name:**

Bit Extension LENGTH 18in. 457.2mm HEX SHANK 5/16in. 7.9mm
HOLE DIA. 23/64in. 9.1mm HEAD DIA. 21/32in. 16.7mm

Cat #:

902-18

UPC #:

02707

Spec:

HEX SHANK 5/16in. 7.9mm USE WITH: 18-5/8 through 18-1; 45-5/8
through 45-13/16; 61PTS-5/8 through 61PTS-1; 66PT-3/8 through
66PT-9/16 and 37154 and 38522 arbors.

Description:

- Extend bit lengths - Holesaw arbors, Spade bits, Nail Eater II® bits, Electrician's bits and Step bits. Use for boring deeper in wood.