



PRODUCT SEARCH

[> SUPP](#)  
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**Installation**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

5/16in. Arbor with Replacement High-Speed Steel Pilot Drill Bit, minimum chuck size 3/8in., Use with 9/16in. - 2in., Point of Purchase Pack

**Cat #:**

02800

**UPC #:**

02800

**Spec:**

Shank: Hex; Shank Size: 5/16in. (7.9mm); Min. Chuck Size: 3/8in. (9.5 mm); Use with 9/16in. - 2in. (14.3-50.8 mm); Weight: 0.5 lb. (227 g)

**Description:**

- The best arbor in the industry ensures a solid connection without any gaps or wobbling.
- Arbors include replaceable, high-speed steel pilot drill.
- Pilot drills have unique split-point tip design.
- Use with Greenlee bimetal hole saws, recessed light hole saws and carbide-grit hole saws (carbide-tipped pilot drill sold separately).
- Can be used with Greenlee #901 or #904 bit extensions.
- Point of Purchase packaging.



© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

**[Privacy Policy](#)** **[Terms of Use](#)** **[Careers](#)**