



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

7/16in. Arbor with Replacement High-Speed Steel Pilot Drill Bit, minimum chuck size 1/2in., Use with 9/16in. - 6in., Point of Purchase Pack

Cat #:

02801

UPC #:

02801

Spec:

Shank: Hex; Shank Size: 7/16in. (11.1mm); Min. Chuck Size: 1/2in. (12.7 mm); Use with 9/16in. - 6in. (14.3-152.4 mm); Weight: 0.5 ls. (227 g)

Description:

- The best arbor in the industry ensures a solid connection without any gaps or wobbling.
- Arbors include replaceable, high-speed steel pilot drill.
- Pilot drills have unique split-point tip design.
- Use with Greenlee bimetal hole saws, recessed light hole saws and carbide-grit hole saws (carbide-tipped pilot drill sold separately).
- Can be used with Greenlee #901 or #904 bit extensions.



© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

[Privacy Policy](#) **[Terms of Use](#)** **[Careers](#)**