



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Rope Diameter: 3/16" (4.8 mm) ROPE LENGTH 600' 182 m AVERAGE
BREAKING STRENGTH 720 lbs. 3.2 kN

Cat #:

409

UPC #:

21468

Spec:

Size 3/16" (4.8 mm) x 600' (182 m) Capacity 720 lbs. (3.2 kN)
average breaking strength Weight 620: 10 lbs. (4.5 kg), 405: 5.2
lbs. (2.4 kg), 409: 5 lbs. (2.3 kg)

Description:

Not for cable pulling. See the ropes listed with cable pullers for recommended cable pulling ropes. Highly visible bright yellow with green runner, excellent for roping off areas on construction sites. Handy reel for dispensing. Rot and mildew resistant. Weather resistant. Economical general purpose rope.

