



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Heavy-Duty Cable Cutter

**Cat #:**

704

**UPC #:**

24564

**Spec:**

704 Length 21" (533 mm) Weight 3.01 lbs. (1.37 kg) Copper Max 350 kcmil (MCM) (150 mm<sup>2</sup>) / Frequent Use 250 kcmil (MCM) (120 mm<sup>2</sup>) Aluminum 500 kcmil (MCM) (240 mm<sup>2</sup>) / Frequent Use 350 kcmil (MCM) (150 mm<sup>2</sup>) Communications Cable 1-3/4" (44 mm) dia.

**Description:**

Strong, lightweight fiberglass handles.

- Adjustable pivot bolt provides for blade adjustment.
- Replaceable, forged, heat treated, and precision ground blades.
- Made in USA.

