



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CONTACT US](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)

**Name:**  
Manual Identer Crimping Tool

**Cat #:**  
1981

**UPC #:**  
06894

**Spec:**

Capacity: Copper color-coded connectors: 8AWG-250 kcmil (MCM)  
Aluminum (dual-rated) color coded connectors: 8 AWG-4/0 AWG  
Length: 22 3/8" (578mm) Weight: 6.8 lb. (3.1 kg)

**Description:**

UL and cUL classified for use with Anderson™, Blackburn®, Burndy, ILSCO, Panduit®, Penn-Union and Thomas & Betts copper and aluminum color-coded lugs and splices.

- Simple screw adjustment for connector size.
- Compact size for getting into tight panels and for easy storage.
- Forged body and handles provide long-term durability.

