



PRODUCT SEARCH

[> SUPP](#)
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**DRILL BITS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**66PT NAIL EATER II® BITS HOLE DIA. 5/8in. 15.9mm HEX SHANK
7/16in. 11.1mm**Cat #:**

66PT-5/8

UPC #:

30919

Spec:

Overall Length 18" (457.2 mm) Twist Length 15" (381 mm)

Description:

Patented new design for improved cutting and cleaner holes. Self-feeding screw point draws bit through wood. Unique patented design cutting angle - smoother starts, reduced cutting loads. Made of super tough heat treated steel; cuts through nails and provides longer life. "Shorty" bits - for working in tight places, yet still can go through three abutting 2 x 4s. See "Bit Extensions" if more length is required (see page 68). P.O.P. packaged.