























Reciprocating Saw Blades

Reciprocating Saw Blades

	Cat. No.	UPC No.	Length x Width x Thickness		Teeth per inch	Type	Application	Quantity per pk.	
			In.	mm					
Metal		353-123	09963	6 x 3/4 x .035	152 x 19.05 x .889	Progressive	Bimetal, Straight	Metal	5
		353-318	09961	4 x 5/16 x .035	101 x 7.938 x .889	18	Bimetal, Scroll	Metal	5
		353-418	09962	4 x 3/4 x .035	101 x 19.05 x .889	18	Bimetal, Straight	Metal	5
		353-614	09964	6 x 3/4 x .035	152 x 19.05 x .889	14	Bimetal, Straight	Metal	5
		353-618	09965	6 x 3/4 x .035	152 x 19.05 x .889	18	Bimetal, Straight	Metal	5
		353-624	09966	6 x 3/4 x .035	152 x 19.05 x .889	24	Bimetal, Straight	Metal	5
		353-804	09977	8 x 3/4 x .050	203 x 19.05 x 1.27	10/14	Bimetal, Straight	Metal	2
		353-814	09975	8 x 3/4 x .050	203 x 19.05 x 1.27	14	Bimetal, Straight	Metal	2
		353-818	09976	8 x 3/4 x .050	203 x 19.05 x 1.27	18	Bimetal, Straight	Metal	2
Wood		353-234	09991	8 x 3/4 x .050	203 x 19.05 x 1.27	Progressive	HCS, Taper	Wood Only	5
		353-656	09967	6 x 3/4 x .050	152 x 19.05 x 1.27	6	Bimetal, Taper	Wood with Nails	5
		353-676	09971	6 x 3/4 x .050	152 x 19.05 x 1.27	6	Bimetal, Scroll	Wood with Nails	5
		353-646	09968	6 x 3/4 x .050	152 x 19.05 x 1.27	6	Bimetal, Straight	Wood with Nails	5
		353-956	09969	9 x 3/4 x .050	228 x 19.05 x 1.27	6	Bimetal, Straight	Wood with Nails	5
		353-156	09970	12 x 3/4 x .050	304 x 19.05 x 1.2	6	Bimetal, Straight	Wood with Nails	5
	Demolition		353-666	09978	6 x 7/8 x .062	152 x 22.23 x 1.56	6	Bimetal, Taper	Wood Demolition
		353-966	09979	9 x 7/8 x .062	228 x 22.23 x 1.56	6	Bimetal, Taper	Wood Demolition	2
		353-669	09980	6 x 7/8 x .062	152 x 22.23 x 1.56	8/10	Bimetal, Taper	Metal Demolition	2
		353-969	09990	9 x 7/8 x .062	228 x 22.23 x 1.56	8/10	Bimetal, Taper	Metal Demolition	2
Specialty			353-345	09972	8 x 3/4 x .050	203 x 19.05 x 1.27	Progressive	Bimetal, Taper	General
		353-636	09973	6 x 3/4 x .050	152 x 19.05 x 1.27	6	Bimetal, Taper	Plaster	5
		353-800	09974	8 x 3/4 x .050	203 x 19.05 x 1.27	Grit	Carbide, Straight	Abrasive Materials	2
Variety	353-VAR	09992		6 x 3/4 x .035 8 x 3/4 x .050 8 x 3/4 x .050	152 x 19.05 x .889 203 x 19.05 x 1.27 203 x 19.05 x 1.27	Progressive Progressive Progressive	353-123 353-234 353-345	Metal Wood Only General	1 1 1