



PRODUCT SEARCH

[> SUPP](#)  
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**Navigation**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

ACTUAL HOLE SIZE 1-1/8in. 28.6 mm HOLE DIAMETER conduit:3/4"  
 PG: Pg-21 copper pipe: 5/8"

**Cat #:**

925-1-1/8

**UPC #:**

10158

**Spec:****Description:**

Made of high-speed steel. Lasts 10 times longer than standard hole saws. Precision-ground teeth cut smooth, burr-free holes with ease. Durability and speed provide low cost per hole. Split-point pilot drill prevents "walking" - makes accurate hole placement easy. Spring-loaded slug ejector saves time. No tool required to change cutter sizes. Less chance of broken teeth because the saw body is machined out of solid, high-speed steel.



© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.

[Privacy Policy](#)[Terms of Use](#)[Careers](#)