



PRODUCT SEARCH

[> SUPP](#)
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Crimping Tool

Cat #:

K111

UPC #:

10763

Spec:

Capacity: 8 AWG - 1 AWG copper color-coded connectors Length: 10" (273 mm) Weight: 1.4 lbs. (0.6 kg)

Description:

Small size and lightweight make this an ideal tool for crimping small lugs and splices.

- Easily fits in tool pouches.
- Full-cycle mechanism assures that crimps are complete.
- Jaws can be opened in mid-cycle if necessary to adjust connector.
- Wide grips make crimping easy on the hands.
- UL and cUL classified with Anderson, Blackburn, Burndy, ILSCO, Panduit, Penn-Union, and Thomas & Betts copper color-coded code connectors.
-

© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.
[Privacy Policy](#)
[Terms of Use](#)
[Careers](#)