



PRODUCT SEARCH



SUPP



DIST

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CONTACT](#)**Tools & Equipment**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Mini Magnetic Bubble Level

Cat #:

L77

UPC #:

11617

Spec:

Length 5-1/2in. (140 mm); Width 3/4in. (19 mm); Height 1-1/2in. (38 mm)

Description:

- Professional grade level with bending offset aid.
- Mini torpedo design with handy 'no-dog' attachment for bending.
- Three rare earth magnets provide superior holding strength.
- Four vial design - 0 deg., 90 deg., 45 deg. and 30 deg.
- Machined from aluminum alloy and anodized to aircraft standards.
- Compact size fits easily in tool pouch.
- V-groove on top of level for easy view of vials.

