



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Two-Hand Ratchet Cable Cutter

**Cat #:**

761

**UPC #:**

11761

**Spec:**

Cutting Capacity: Copper- 1000 kcmil (MCM) (500 mm<sup>2</sup>); Aluminum- 1000 kcmil (MCM) (500 mm<sup>2</sup>); Communications Cable- 1-1/8" dia. (28 mm<sup>2</sup>) Length: 10-3/4" (273 mm) Weight: 3.6 lbs. (1.6 kg)

**Description:**

Two-handed operation provides more leverage and makes cutting large cables easier.

- Short fiberglass handles make it easy to use in tight places and to store in tool boxes.
- Single speed ratchet mechanism.
- Blade release allows blades to be opened in mid-cut.
- Heavy duty forged steel blades provide long life.

