



PRODUCT SEARCH

[> SUPP](#)
[> DIST](#)
[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**DRILLING**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &
Miscellaneous](#)**Name:**

SIZE 1-1/8in. 28.6mm MIN CHUCK SIZE 3/8in. 9.5mm CONDUIT
 SIZE 3/4" PG 21

Cat #:

625-1-1/8

UPC #:

38328

Spec:

Maximum Cutting Depth 8 Ga. (4 mm)

Description:

Multiple tungsten carbide tips for long life and smooth cutting. Cut fast, accurate, high quality holes in stainless steel, copper, aluminum, steel. Flange stop prevents over drilling. Replaceable cobalt steel pilot drill, with split point tip design, to improve performance and resist walking; eliminates need for "center punch."

© 2007 Greenlee Textron Inc., a subsidiary of **Textron Inc.** All rights reserved.

[Privacy Policy](#) [Terms of Use](#) [Careers](#)