

PRODUCT SEARCH

[> SUPPLIER CENTER](#)]
[> DISTRIBUTOR CENTER](#)]

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[COMPANY INFO](#)**PRODUCTS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &
Miscellaneous](#)**Name:**

LED Penlight

Cat #:

FL2AAAP

UPC #:

13493

Spec:

Size: 5.2 x .8 in / 132 x 21 mm

Weight: 1.5 oz / 43 g

Batteries: (2) AAA Alkaline / LR3

Brightness: 7 lumens

Distance Seen: 46 ft / 14 m

Burn Time: 14-15 hr

Waterproof Depth: 3 ft / 1 m

Description:

- Batteries are included.
- Powerful LED's in compact form.
- Rugged, all-weather construction.
- Attachment accessories for added ease-of-use and increased versatility.
- FL2AAAPM, FL4AAP and FLHEAD offer a hands-free option.

Instruction Manual(s):© 2010 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.[Privacy Policy](#)[Terms of Use](#)[Careers](#)[Idea Submissions](#)