



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &](#)[Miscellaneous](#)**Name:**

High Leverage Side-Cutting Pliers 9" molded grip

Cat #:

0151-09M

UPC #:

54702

Spec:

Overall Length: 9-3/8"(23.8 cm) Weight: 1.13 lbs(.51 kg)

Description:

Custom grip allows area for user identification.

- Slip-proof, ergonomic molded grips for increased comfort and reduced user fatigue.
- Wider grip design provides larger load bearing area.
- Location of handle ridge allows for users to "choke up" for greater control.
- High leverage pliers design and diamond-serrated jaws for optimum cutting and gripping performance.
- Forged from chrome vanadium steel for greater durability and strength.
- Precision-machined and induction-hardened blades strengthen cutters and provide consistent performance.
- Effectively cuts hardened wire, ACSR, bolts, screws, and nails.
- Through-hardened steel for longer life.
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

© 2007 Greenlee Textron Inc., a subsidiary of [Textron Inc.](#) All rights reserved.[Privacy Policy](#)[Terms of Use](#)[Careers](#)