



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

High Leverage Diagonal Cutting Pliers 8" angled molded grip

Cat #:

0251-08AM

UPC #:

54740

Spec:

Overall Length: 8-3/4"(22 cm) Weight: .85 lbs(.39 kg)

Description:

Custom grip allows area for user identification.

- Flared handles for added comfort and leverage.
- Wider grip design provides larger load bearing area for user comfort.
- Forged from chrom vanadium steel for greater durability and strength.
- Precision-machined and induction-hardened blades strengthen cutters and provide consistent performance.
- Effectively cuts most hardened wire, ACSR, bolts, screws, and nails.
- Through-hardened steel for longer life.
- Dual cutting edges for optimum cutting performance.
- Exceeds ASME/ANSI specifications.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

