



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**Navigation**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &](#)[Miscellaneous](#)**Name:**

100' x 1/4" x .060" (30.5 m x 6.4 mm x 1.5 mm) Steel Fish Tape in Winder Case

Cat #:

538-10

UPC #:

30394

Spec:

Capacity 1/8" (3.2 mm) and 1/4" (6.4 mm) tape width - 400 lbs. (1.7 kN) maximum design strength. Weight 438-10 - 5 lbs. (2.3 kg) R438-10 - 3 lbs. (1.4 kg) R538-10 - 6 lbs. (2.7 kg) 438-20 - 7 lbs. (3.2 kg) R438-20 - 6 lbs. (2.7 kg) R538-20 - 11 lbs. (5 kg) R438-5 - 2 lbs. (0.9 kg) 538-10 - 8 lbs. (3.6 kg)

Description:

High-impact nylon, one-piece handle for maximum durability, long life, and easy, comfortable use.

- Large handle grip for greater user control.
- Self-tensioning case for easy tape winding. (No tension trigger.)
- Wide, impact-resistant rewinder case with viewports to ensure tape fit and retaining strap on inside to hold tape secure.
- Dirt-free tape finish keeps hands cleaner during use.

