

PRODUCT SEARCH

SUPP

HOME

WHAT'S NEW

**SERVICE / SUPPORT** 

WHERE TO BUY

INSTRUCTION MANUALS

СО

## 220DUC

Hand Tools Holemaking Bending Fishing

Cable Pulling

Wire & Cable Termination

Voice Data Video

Testing & Measurement

Storage & Material Handling

Hydraulic Pumps & Miscellaneous



## Name:

SITE-RITE® Hand Bender with handle for 1" EMT, 3/4" Rigid

Cat #

842H

**UPC** #: 32919

## Spec:

Capacity 1/2" - 1-1/4" EMT, 1/2" - 1" Rigid Weight 840 - 1.4 lbs. (.7 kg) 8840 - 3.1 lbs. (1.4 kg) 840H - 5.5 lbs. (2.5 kg) 8841 - 4.3 lbs. (2.0 kg) 841 - 2.1 lbs. (0.9 kg) 8842 - 7.2 lbs. (3.3 kg) 841H - 6.4 lbs. (2.9 kg) 8843 - 16.2 lbs. (7.3 kg) 842 - 3.5 lbs. (1.6 kg) 8840H - 7 lbs. (3.2 kg) 842H - 11 lbs. (5 kg) 8841H - 9 lbs. (4.1 kg) 843 - 8.3 lbs. (3.8 kg) 8842H - 15 lbs. (6.8 kg)

## Description:

Handle straight up and down for 30 degree bends.

- Patented sight indicator on bender is a key feature for bending angles fast and easy.
- Non-slip, contoured pedal for added leverage.
- Strong, stable square hook design.
- Cast-in markings for stub-ups, saddle bends, back-to-back bends, and head-up or down bending.

•

© 2007 Greenlee Textron Inc., a subsidiary of Textron Inc. All rights reserved.

Privacy Policy Terms of Use Careers