



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

MINI GLO STIX KIT - 8'

Glo Stix Kit: 3/16 x 8' long with bullet & J hook nose tips



Image  
Unavailable

Cat No: 52047692

UPC No: 783310129189

### Description

---

- Luminescent fiberglass rods glow in the dark to make fishing voice, data and video wires easier in dark spaces, such as above ceilings, in walls, and below sub-floors
- More flexible for fishing in walls through outlet box holes
- Sturdy, steel-threaded connectors are interchangeable with Greenlee 1/4 IN (6.4 mm) Fish Stix
- Clear, non-metallic storage tube keeps Glo Stix charged and ready to use
- 200 lbs. (0.9 kN) maximum pulling strength
- Optional Whisk Nose Tip is available for fishing over obstacles, and can be used to guide extended Glo Stix sideways above ceilings by rotating. Can also be used to fish longer lengths by providing a tip that can be snagged from the opposite direction with another extended Fish or Glo Stix with a hook nose tip.

### Specifications

---

- Accessory : 10497 Hook Nose Tip, 10498 Bullet Nose Tip, 11426 Whisk Nose Tip
- Diameter : 3/16 IN (4.700 MM)
- Includes : Bullet And "J" Hook Nose Tips
- Length : 8.000 FT
- Minimum Bend Radius : 4-1/4 IN (108.000 MM)
- Replacement Part : 11583 1/4 IN X 4 FT Fish Stix Section, 11584 1/4 IN X 6 FT Fish Stix Section, 12920 3/16 IN X 20 IN Glo Stix Section, 11585 3/16 IN x 3 FT Glo Stix Section, 11427 3/16 IN x 5 FT Glo Stix Section, 12922 5/32 IN X 4 FT Glo Stix Section, 89803 5/32 IN X 6 FT
- Section Length : 20.000 IN (0.500 M)
- Sections : 5
- Sub Brand : Glo Stix
- Tensile Strength : 200.000 LB (0.900 KN) Maximum Pulling Strength
- Weight : 0.800 LB (0.400 KG)