



4 Ton Crimper, Li-Ion, standard, 230V AC

4 Ton Crimper, Li-Ion, standard, 230V AC

Cat No: EK410LX230

UPC No: 783310609315

## Description

---

Equipped with Bluetooth™ Communication enabled via the Greenlee Gator Eye app. Features LED display screen communicating pressure and battery levels as well as tool diagnostics with real-time tool feedback.

- Intelligent Crimping System Technology includes a pressure sensor that monitors the crimping force of each crimp and provides the operator a visual and audible alert if the force is belows specifications
- State of the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times
- LED light provides the operator with the battery charge and tool maintenance status
- In Line tool style is light weight and very easy to control
- One trigger controls all tool functions
- Crimping head rotates 350°
- Tools automatically retract when the crimping cycle is complete
- Overmolded tacky grip areas make gripping the tool easier and more comfortable
- LED work light illuminates dark work areas
- Greenlee battery-powered crimping tools now use bio-degradable oil
- Smart chargers control the charging current, charging voltage and battery temperature to maximize battery life
- Used with Greenlee KC4, KA4 and KD4 crimping dies
- Available with 120V, 12V or 230V battery charger or with 120V or 230V corded adapter in place of batteries and charger

## Specifications

---

- Sub Brand : Gator
- Type : Die style crimper
- Application : 4 Ton Crimping
- Standard : C/US UL Listed
- Wire Size :
  - 8 AWG - 300 kcmil Cu
  - 8 AWG - 2/0 kcmil Al
- Overall Length : 13.25 IN (337mm)
- Crimping Force : 7,900 lbs. (35 kN)
- Crimping Capacity :
  - 300 kcmil (MCM) Copper
  - 2/0 AWG Al
- Connector Type : Color-coded lugs and splices
- Handle Type : In-Line Style with over molded rubber grip