

Milwaukee

Nothing but **HEAVY DUTY.**

MILWAUKEE TOOL SPECIALS!

M18™ CORDLESS 2-TOOL COMBO KIT 2691-22

- M18™ ½" Compact Drill/Driver Delivers 400 In-lbs of Torque and is Only 4 lbs. and 7 ¾" Long
- M18™ ¼" Hex Compact Impact with the Milwaukee 4-Pole Frameless Motor Delivers 1400 In-lbs. of torque



M18 CORDLESS COMPACT DRILL DRIVER 2601-22

- 1/2 in. Ratcheting Chuck with plastic sleeve
- Heavy-Duty 2-Speed Metal Gear Box: 0-350/0-1,400 rpm
- Compact Length (7-3/4 in.) fits in tight areas
- Compact Motor delivers 400 in.-lbs. of maximum torque
- Built-in LED light illuminates work surfaces
- Lightweight 4.0 lbs.



M18™ CORDLESS METAL SAW KIT 2682-22

- No Load RPM 3600
- Battery Pack Replacement 2PYZ8
- Blade Side Right, Shoe Material Stainless Steel, Bearings Ball and Roller, Standards UL Listed
- CSA Certified, Includes (2) 2PYZ8 Batteries, 4PKV9 1-hr Charger, Carbide-Tipped Blade
- Contractor Bag



M18 CORDLESS 2-TOOL COMBO KIT 2697-22

- M18™ ½" Hammer Drill Driver with Milwaukee® 4-Pole Frameless Motor delivers 550 in-lbs of peak torque, 0-450/0-1,700 RPM, & 29,000 BPM
- M18™ ¼" Hex Compact Impact Driver featuring a Milwaukee® Designed Impact Mechanism for 1,400 in-lbs of torque
- DPM™ - Digital Power Management: Overload protection prevents damage to the tool and battery in abusive situations



M18™ CORDLESS 2-TOOL COMBO KIT 2698-22

- M18™ ½" Hammer Drill Driver with Milwaukee® 4-Pole Frameless Motor delivers 550 in-lbs of peak torque, 0-450/0-1,700 RPM, & 29,000 BPM
- M18™ 5-3/8" Metal Saw with Milwaukee® 4-Pole Frameless Motor delivers 3,600 RPM for up to 20% faster cuts and 40% more run-time



M18™ CORDLESS 4-TOOL COMBO KIT 2694-24

- M18™ Cordless ½" Hammer Drill / Driver
- M18™ Cordless Sawzall® Reciprocating Saw
- M18™ Cordless 6-½" Circular Saw Delivers 3,500 RPM with Magnesium Upper and Lower Guards for Maximum Durability

