



The frosted lens on **ICE LAMPS** provide soft no glare illumination, eliminating dark lines and shadows.



Order code	Description	Watts (W)	Base	Volts (V)	Beam angle (°)	Beam spread	CBCP (cd)	Average life (hrs)	Initial lumens (lm)	Case qty	
<b>ES16</b>											
MOL : 2 1/2 in. (55 mm) Dia. : 2 in. (51 mm)											
55052	H20GU10/CG/2.5M/120V/STD ICE	20	GU10	120	40	Flood	300	2500	130	200	
55051	H35GU10/CG/2.5M/120V/STD ICE	35	GU10	120	40	Flood	600	2500	280	200	
55038	H50GU10/CG/2.5M/120V/STD ICE	50	GU10	120	40	Flood	840	2500	500	200	
55037	H50GU10/CG/2.5M/130V/STD ICE	50	GU10	130	40	Flood	840	2500	375	200	
<b>MR16</b>											
MOL : 1 7/8 in. (45 mm) Dia. : 2 in. (51 mm)											
55039	H50MR16/5M/GX5.3/12V/STD ICE	50	GX5.3	12	N/A	Flood	N/A	5000	850	200	
<b>PAR20</b>											
MOL : 3 1/2 in. (82 mm) Dia. : 2.5 in. (63.5 mm)											
*50185 <sup>†</sup>	H50PAR20/NFL/2.5M/120V/STD ICE	50	E26	120	N/A	Narrow Flood	N/A	2500	500	15	
*50184 <sup>†</sup>	H50PAR20/NFL/5M/130V/STD ICE	50	E26	130	N/A	Narrow Flood	N/A	5000	375	15	
<b>PAR30</b>											
MOL : 3 3/4 in. (93 mm) Dia. : 3 3/4 in. (95 mm)											
*50187	H50PAR30/FL/2.5M/120V/STD ICE	50	E26	120	N/A	Flood	N/A	2500	600	15	
*50186 <sup>†</sup>	H50PAR30/FL/5M/130V/STD ICE	50	E26	130	N/A	Flood	N/A	5000	450	15	
*50191	H75PAR30/FL/2.5M/120V/STD ICE	75	E26	120	N/A	Flood	N/A	2500	990	15	
*50190	H75PAR30/FL/5M/130V/STD ICE	75	E26	130	N/A	Flood	N/A	5000	745	15	
<b>PAR30LN</b>											
MOL : 4 1/4 in. (122 mm) Dia. : 3 3/4 in. (95 mm)											
*50189	H50PAR30/LN/FL/2.5M/120V/STD ICE	50	E26	120	N/A	Flood	N/A	2500	600	15	
*50188 <sup>†</sup>	H50PAR30/LN/FL/5M/130V/STD ICE	50	E26	130	N/A	Flood	N/A	5000	450	15	
*50193	H75PAR30/LN/FL/2.5M/120V/STD ICE	75	E26	120	N/A	Flood	N/A	2500	990	15	
*50192	H75PAR30/LN/FL/5M/130V/STD ICE	75	E26	130	N/A	Flood	N/A	5000	745	15	
<b>PAR38</b>											
MOL : 5 1/4 in. (135 mm) Dia. : 4 3/4 in. (121 mm)											
*50971 <sup>†</sup>	H45PAR38/FL/2.5M/MS/120V/STD ICE	45	E26SKT	120	N/A	Flood	N/A	2500	460	15	
*50970 <sup>†</sup>	H45PAR38/FL/5M/MS/130V/STD ICE	45	E26SKT	130	N/A	Flood	N/A	5000	345	15	
*50733	H75PAR38/FL/2.5M/MS/120V/STD ICE	75	E26SKT	120	N/A	Flood	N/A	2500	990	15	
*51053 <sup>†</sup>	H75PAR38/FL/5M/MS/130V/STD ICE	75	E26SKT	130	N/A	Flood	N/A	5000	745	15	
*50195 <sup>†</sup>	H90PAR38/FL/2.5M/MS/120V/STD ICE	90	E26SKT	120	N/A	Flood	N/A	2500	1140	15	
*50194 <sup>†</sup>	H90PAR38/FL/5M/MS/130V/STD ICE	90	E26SKT	130	N/A	Flood	N/A	5000	860	15	



<sup>†</sup>This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.  
\* Cannot be sold in Ontario as per provincial regulations on energy efficiency of lighting products.

# ICE Lamps