

Order code	Description	Watts (W)	Base	Volts (V)	Finish/ Colour	Average life (hrs)	Filament	Case qty
A19 Transparent								
MOL : 4 1/4 in. (108 mm) LCL : 2 2/32 in. (72 mm)								
52092	60A19/TG/5M/130V/STD	60	E26	130	Transparent green	5000	C-9	24
52041	60A19/TR/5M/130V/STD	60	E26	130	Transparent red	5000	C-9	24
52093	60A19/TY/5M/130V/STD	60	E26	130	Transparent yellow	5000	C-9	24
52098	100A19/TA/5M/130V/STD	100	E26	130	Transparent amber	5000	C-9	24
52099	100A19/TB/5M/130V/STD	100	E26	130	Transparent blue	5000	C-9	24
52100	100A19/TG/5M/130V/STD	100	E26	130	Transparent green	5000	C-9	24
52101	100A19/TR/5M/130V/STD	100	E26	130	Transparent red	5000	C-9	24
B10								
MOL : 3 1/2 in. (89 mm) LCL : 1 2/32 in. (47 mm)								
52152	40B10/WH/3M/130V/STD	40	E26	130	White	3000	C-7A	500
52151	60B10/WH/3M/E12/130V/STD	60	E12	130	White	3000	C-7A	500
BR30								
MOL : 5 29/32 in. (137 mm) LCL : 3 1/8 in. (86 mm)								
52027	75BR30/A/FL/5M/130V/STD	75	E26	130	Amber	5000	C-9	24
52028	75BR30/B/FL/5M/130V/STD	75	E26	130	Blue	5000	C-9	24
52029	75BR30/G/FL/5M/130V/STD	75	E26	130	Green	5000	C-9	24
52030	75BR30/P/FL/5M/130V/STD	75	E26	130	Pink	5000	C-9	24
52031	75BR30/R/FL/5M/130V/STD	75	E26	130	Red	5000	C-9	24
52032	75BR30/Y/FL/5M/130V/STD	75	E26	130	Yellow	5000	C-9	24
BR30 Transparent								
MOL : 5 29/32 in. (137 mm) LCL : 3 1/8 in. (86 mm)								
10083	75BR30/TA/5M/130V/STD	75	E26	130	Transparent amber	5000	C-9	24
10104	75BR30/TG/5M/130V/STD	75	E26	130	Transparent green	5000	C-9	24
10139	75BR30/TP/5M/130V/STD	75	E26	130	Transparent pink	5000	C-9	24
10082	75BR30/TR/5M/130V/STD	75	E26	130	Transparent red	5000	C-9	24
10080	75BR30/TY/5M/130V/STD	75	E26	130	Transparent yellow	5000	C-9	24
10081	75BR30/TB/5M/130V/STD	75	E26	130	Transparent blue	5000	C-9	24
BR38								
MOL : 5 29/32 in. (147 mm) LCL : 3 3/32 in. (83 mm)								
50093	100BR38/A/5M/130V/STD	100	E26	130	Amber	5000	C-9	12
50095	100BR38/G/5M/130V/STD	100	E26	130	Green	5000	C-9	12
50097	100BR38/R/5M/130V/STD	100	E26	130	Red	5000	C-9	12
50098	100BR38/Y/5M/130V/STD	100	E26	130	Yellow	5000	C-9	12
BR40								
MOL : 6 1/2 in. (165 mm) LCL : 3 3/8 in. (86 mm)								
52136	150BR40/A/FL/5M/130V/STD	150	E26	130	Amber	5000	C-9	12
52137	150BR40/G/FL/5M/130V/STD	150	E26	130	Green	5000	C-9	24
52068	150BR40/R/FL/5M/130V/STD	150	E26	130	Red	5000	C-9	12
52069	150BR40/Y/FL/5M/130V/STD	150	E26	130	Yellow	5000	C-9	12
F10								
MOL : 2 2/2 in. (76 mm) LCL : 1 29/32 in. (43 mm)								
14459	15F10/WH/1.5M/E12/130V	15	E12	130	White	1500	C-7A	250
MOL : 3 1/16 in. (78 mm) LCL : 1 29/32 in. (43 mm)								
14456	15F10/A/2.5M/E12/130V	15	E12	130	Amber	2500	C-7A	250
14460	25F10/A/2.5M/E12/130V	25	E12	130	Amber	2500	CC-2V	250
F15								
MOL : 4 1/4 in. (108 mm) LCL : 2 9/16 in. (65 mm)								
50756	25F15/A/1.5M/130V/STD	25	E26	130	Amber	1500	CC-2V	500
50753	25F15/WH/1.5M/130V/STD	25	E26	130	White	1500	CC-2V	500
50757	40F15/A/1.5M/130V/STD	40	E26	130	Amber	1500	CC-2V	500
50754	40F15/WH/1.5M/130V/STD	40	E26	130	White	1500	CC-2V	500
50758	60F15/A/1.5M/130V/STD	60	E26	130	Amber	1500	CC-2V	500
G11								
MOL : 2 3/16 in. (59 mm) LCL : 1 3/8 in. (41 mm)								
50763	7.5G11/CB/1M/130V/STD	7.5	E26	130	Ceramic blue	1000	C-5	500
50764	7.5G11/CG/1M/130V/STD	7.5	E26	130	Ceramic green	1000	C-5	500
50765	7.5G11/CO/1M/130V/STD	7.5	E26	130	Ceramic orange	1000	C-5	500
50766	7.5G11/CR/1M/130V/STD	7.5	E26	130	Ceramic red	1000	C-5	500
50760	7.5G11/WH/1M/E12/130V/STD	7.5	E12	130	White	1000	C-5	500
50762	7.5G11/WH/1M/130V/STD	7.5	E26	130	White	1000	C-5	500
50767	7.5G11/CY/1M/130V/STD	7.5	E26	130	Ceramic Yellow	1000	C-5	500
50769	7.5G11/TR/1M/130V/STD	7.5	E26	130	Transparent red	1000	C-5	500