

## Features

- Longer life
- Uses less energy
- Brighter than conventional lamps
- Available in a wide variety of shapes, colours, sizes and wattages

## Applications

- Residential
- Retail stores
- Track lighting
- Jewelry boutiques
- Wall washing

PAR20



MOL = 3 7/8 in. (82 mm)  
Dia. = 2 1/2 in. (64 mm)

PAR30



MOL = 3 21/2 in. (93 mm)  
Dia. = 3 1/4 in. (95 mm)

Order code	Description	Watts (W)	Base	Volts (V)	Finish	Beam angle (°)	Average life (hrs)	Mean lumens (lm)	Case qty
55564	H50PAR20/NFL/2.5M/120V/ELUME	50	E26	120	Clear	30	2 500	550	120
57655	H50PAR30/FL/5M/130V/ELUME	50	E26	130	Clear	35	5 000	495	15

E-Lume Satin lamps offer comfortable lighting while softening the appearance of dark lines and shadows. An overall gentle effect can be achieved when using these lamps. Ideal for soft, even, lighting applications.

## Features

- Uniform and glare-free lighting
- Diminishes dark lines and shadows
- Indoor or outdoor use

## Applications

- Residential
- Retail
- Commercial
- Ambient lighting

PAR20



MOL = 3 7/8 in. (82 mm)  
Dia. = 2 1/2 in. (64 mm)

PAR30



MOL = 3 21/2 in. (93 mm)  
Dia. = 3 1/4 in. (95 mm)

PAR30LN



MOL = 4 13/16 in. (122 mm)  
Dia. = 3 3/4 in. (95 mm)

PAR38



MOL = 5 1/4 in. (135 mm)  
Dia. = 4 3/4 in. (121 mm)

Order code	Description	Watts (W)	Base	Volts (V)	Finish	Average life (hrs)	Mean lumens (lm)	Case qty
<sup>1</sup> 59753	H50PAR20/NFL/5M/130V/ELUME SAT	50	E26	130	Frost	5 000	375	15
<sup>1</sup> 59751	H50PAR20/NFL/2.5M/120V/ELUME SAT	50	E26	120	Frost	2 500	500	15
<sup>1</sup> 59754	H75PAR30/FL/5M/130V/ELUME SAT	75	E26	130	Frost	5 000	745	15
<sup>1</sup> 59750	H90PAR38/FL/MS/5M/130V/ELUME SAT	90	E26SKT	130	Frost	5 000	1 140	15
<sup>1</sup> 59756	H90PAR38/FL/MS/2.5M/120V/ELUME SAT	90	E26SKT	120	Frost	2 500	855	15

<sup>1</sup>This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.