



Plug-in lamps provide even light distribution and stay brighter longer with an average life of 12 000 hours. They are ideal for interior lighting.

Operating temperatures: -10°C/14°F to 70°C/158°F

TWIN TUBE




Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty
Twin Tube								
MOL: 4 1/8 in. (105 mm)								
50803	PL5/27K/TT/2P/STD	5	G23	2 700	82	12 000	250	96
50805	PL5/41K/TT/2P/STD	5	G23	4 100	82	12 000	250	96
MOL: 5 1/16 in. (135 mm)								
50806	PL7/27K/TT/2P/STD	7	G23	2 700	82	12 000	400	96
50807	PL7/35K/TT/2P/STD	7	G23	3 500	82	12 000	400	96
50808	PL7/41K/TT/2P/STD	7	G23	4 100	82	12 000	400	96
MOL: 6 1/2 in. (165 mm)								
14002	PL9/BLB/TT/2P/STD	9	G23	Black Light Blue	82	12 000	N/A	96
50810	PL9/27K/TT/2P/STD	9	G23	2 700	82	12 000	600	96
50811	PL9/35K/TT/2P/STD	9	G23	3 500	82	12 000	600	96
50812	PL9/41K/TT/2P/STD	9	G23	4 100	82	12 000	600	96
50813	PL9/50K/TT/2P/STD	9	G23	5 000	82	12 000	600	96
MOL: 7 1/32 in. (180 mm)								
50816	PL13/27K/TT/2P/STD	13	GX23	2 700	82	12 000	900	96
50817	PL13/30K/TT/2P/STD	13	GX23	3 000	82	12 000	900	96
50818	PL13/35K/TT/2P/STD	13	GX23	3 500	82	12 000	900	96
50819	PL13/41K/TT/2P/STD	13	GX23	4 100	82	12 000	900	96
50820	PL13/50K/TT/2P/STD	13	GX23	5 000	82	12 000	900	96
Double Tube								
MOL: 4 1/32 in. (110 mm)								
50976	PL9/27K/DTT/2P/STD	9	G23-2	2 700	82	12 000	600	96
50977	PL9/35K/DTT/2P/STD	9	G23-2	3 500	82	12 000	600	96
MOL: 4 1/32 in. (118 mm)								
50978	PL13/27K/DTT/2P/STD	13	GX23-2	2 700	82	12 000	900	96
50979	PL13/30K/DTT/2P/STD	13	GX23-2	3 000	82	12 000	900	96
50980	PL13/35K/DTT/2P/STD	13	GX23-2	3 500	82	12 000	900	96
50981	PL13/41K/DTT/2P/STD	13	GX23-2	4 100	82	12 000	900	96
MOL: 5 1/32 in. (152 mm)								
50982	PL18/27K/DTT/2P/STD	18	G24d-2	2 700	82	12 000	1 200	96
50984	PL18/35K/DTT/2P/STD	18	G24d-2	3 500	82	12 000	1 200	96
50985	PL18/41K/DTT/2P/STD	18	G24d-2	4 100	82	12 000	1 200	96
MOL: 4 1/32 in. (110 mm)								
51055	PL9/41K/DTT/2P/STD	9	G23-2	4 100	82	12 000	600	96
MOL: 6 1/8 in. (110 mm)								
57831	PL28/27K/DTT/2P/STD	28	GX32d-3	2 700	82	12 000	1 600	96
MOL: 6 1/16 in. (173 mm)								
50986	PL26/27K/DTT/2P/STD	26	G24d-3	2 700	82	12 000	1 800	96
50987	PL26/30K/DTT/2P/STD	26	G24d-3	3 000	82	12 000	1 800	96
50988	PL26/35K/DTT/2P/STD	26	G24d-3	3 500	82	12 000	1 800	96
50989	PL26/41K/DTT/2P/STD	26	G24d-3	4 100	82	12 000	1 800	96

DOUBLE TWIN TUBE



2-Pin Plug-in Lamps



TWIN TUBE



TWIN TUBE LONG



DOUBLE TWIN TUBE



TRIPLE TWIN TUBE



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty
Twin Tube								
MOL : 6 3/16 in. (157 mm)								
50829	PL13/27K/TT/4P/STD	13	2GX7	2 700	82	12 000	900	96
50830	PL13/30K/TT/4P/STD	13	2GX7	3 000	82	12 000	900	96
50831	PL13/41K/TT/4P/STD	13	2GX7	4 100	82	12 000	900	96
Twin Tube Long								
MOL : 8 15/16 in. (227 mm)								
10090	PL18/30K/L/4P/STD	18	2G11	3 000	82	12 000	1 250	50
10091	PL18/35K/L/4P/STD	18	2G11	3 500	82	12 000	1 250	50
10092	PL18/41K/L/4P/STD	18	2G11	4 100	82	12 000	1 250	50
MOL : 12 3/32 in. (323 mm)								
10093	PL24/30K/L/4P/STD	24	2G11	3 000	82	12 000	1 800	50
10094	PL24/35K/L/4P/STD	24	2G11	3 500	82	12 000	1 800	50
10095	PL24/41K/L/4P/STD	24	2G11	4 100	82	12 000	1 800	50
MOL : 16 15/32 in. (418 mm)								
10096	PL36/30K/L/4P/STD	36	2G11	3 000	82	12 000	2 900	50
10097	PL36/35K/L/4P/STD	36	2G11	3 500	82	12 000	2 900	50
10098	PL36/41K/L/4P/STD	36	2G11	4 100	82	12 000	2 900	50
MOL : 21 1/8 in. (535 mm)								
10102	PL55/35K/L/4P/STD	55	2G11	3 500	82	12 000	4 800	50
10103	PL55/41K/L/4P/STD	55	2G11	4 100	82	12 000	4 800	50
MOL : 22 17/32 in. (572 mm)								
10099	PL40/30K/L/RS/4P/STD	40	2G11	3 000	82	12 000	3 150	50
10100	PL40/35K/L/RS/4P/STD	40	2G11	3 500	82	12 000	3 150	50
10101	PL40/41K/L/RS/4P/STD	40	2G11	4 100	82	12 000	3 150	50
Double Twin Tube								
MOL : 5 1/2 in. (131 mm) Dia. : 5 1/2 in. (139.5 mm)								
50835	PL13/27K/DTT/4P/STD	13	G24q-1	2 700	82	12 000	900	96
50836	PL13/30K/DTT/4P/STD	13	G24q-1	3 000	82	12 000	900	96
50837	PL13/35K/DTT/4P/STD	13	G24q-1	3 500	82	12 000	900	96
50838	PL13/41K/DTT/4P/STD	13	G24q-1	4 100	82	12 000	900	96
MOL : 5 9/16 in. (147 mm)								
50839	PL18/27K/DTT/4P/STD	18	G24q-2	2 700	82	12 000	1 200	96
50840	PL18/30K/DTT/4P/STD	18	G24q-2	3 000	82	12 000	1 200	96
50841	PL18/35K/DTT/4P/STD	18	G24q-2	3 500	82	12 000	1 200	96
50842	PL18/41K/DTT/4P/STD	18	G24q-2	4 100	82	12 000	1 200	96
MOL : 6 1/2 in. (165 mm)								
50843	PL26/27K/DTT/4P/STD	26	G24q-3	2 700	82	12 000	1 800	96
50844	PL26/30K/DTT/4P/STD	26	G24q-3	3 000	82	12 000	1 800	96
50845	PL26/35K/DTT/4P/STD	26	G24q-3	3 500	82	12 000	1 800	96
50846	PL26/41K/DTT/4P/STD	26	G24q-3	4 100	82	12 000	1 800	96
Triple Twin Tube								
MOL : 4 3/16 in. (116 mm)								
50851	PL18/27K/TTT/4P/STD	18	GX24q-2	2 700	82	12 000	1 200	96
50852	PL18/30K/TTT/4P/STD	18	GX24q-2	3 000	82	12 000	1 200	96
50853	PL18/35K/TTT/4P/STD	18	GX24q-2	3 500	82	12 000	1 200	96
50854	PL18/41K/TTT/4P/STD	18	GX24q-2	4 100	82	12 000	1 200	96
MOL : 5 1/2 in. (131 mm)								
50855	PL26/27K/TTT/4P/STD	26	GX24q-3	2 700	82	12 000	1 800	96
50856	PL26/30K/TTT/4P/STD	26	GX24q-3	3 000	82	12 000	1 800	96
50857	PL26/35K/TTT/4P/STD	26	GX24q-3	3 500	82	12 000	1 800	96
50858	PL26/41K/TTT/4P/STD	26	GX24q-3	4 100	82	12 000	1 800	96
MOL : 5 9/16 in. (147 mm)								
50865	PL32/27K/TTT/4P/STD	32	GX24q-3	2 700	82	12 000	2 400	96
50859	PL32/30K/TTT/4P/STD	32	GX24q-3	3 000	82	12 000	2 400	96
50860	PL32/35K/TTT/4P/STD	32	GX24q-3	3 500	82	12 000	2 400	96
50861	PL32/41K/TTT/4P/STD	32	GX24q-3	4 100	82	12 000	2 400	96
MOL : 6 1/2 in. (165 mm)								
50862	PL42/30K/TTT/4P/STD	42	GX24q-4	3 000	82	12 000	3 200	96
50863	PL42/35K/TTT/4P/STD	42	GX24q-4	3 500	82	12 000	3 200	96
50864	PL42/41K/TTT/4P/STD	42	GX24q-4	4 100	82	12 000	3 200	96

4-Pin Plug-in Lamps