



IS=Instant Start ballast PS=Program Start ballast PRS=Program Rapid Start ballast

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS (3 hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length in. (mm)	Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	-----------------------	---------------------	------------------	-------------------------	-----------------	----------

### Circline

Dia. : 1 3/16 in. (30 mm)

58984	FC6T9/CW/RS/4P/STD	20	G10q-4	4 100	82	10 000	890	850	7 (165)	45	12
58985	FC8T9/WW/RS/4P/STD	22	G10q-4	3 000	82	10 000	1 450	1 380	8 (210)	66	12
58983	FC8T9/CW/RS/4P/STD	22	G10q-4	4 100	82	10 000	1 350	1 280	8 (210)	61	24
58982	FC8T9/DL/RS/4P/STD	22	G10q-4	6 500	82	10 000	1 210	1 150	8 (210)	55	24
58986	FC12T9/CW/RS/4P/STD	32	G10q-4	4 100	82	10 000	2 300	2 185	12 (305)	72	24
58987	FC12T9/DL/RS/4P/STD	32	G10q-4	6 500	82	10 000	2 000	1 900	12 (305)	63	12
58988	FC16T9/CW/RS/4P/STD	40	G10q-4	4 100	82	10 000	3 150	3 000	16 (406)	79	12

### U-bent

Dia. : 1 in. (26 mm)

#### 700 series

10480	FB32T8/35K/7/U6/RS/G13/STD ESV	32	G13*	3 500	75	20 000	2 450	2 200	22.5 (572)	77	20
10481	FB32T8/41K/7/U6/RS/G13/STD ESV	32	G13	4 100	75	20 000	2 450	2 200	22.5 (572)	77	20

#### 800 series

57522	FB28T8/30K/8/U6/RS/G13/STD	28	G13	3 000	85	20 000	2 600	2 350	22.5 (572)	93	20
57519	FB28T8/35K/8/U6/RS/G13/STD	28	G13	3 500	85	20 000	2 600	2 350	22.5 (572)	93	20
57518	FB28T8/41K/8/U6/RS/G13/STD	28	G13	4 100	85	20 000	2 600	2 350	22.5 (572)	93	20
58698	FB31T8/35K/8/U1/RS/G13/STD	31	G13	3 500	82	24 000	2 750	2 610	22.5 (572)	89	20
58697	FB31T8/41K/8/U1/RS/G13/STD	31	G13	4 100	82	24 000	2 750	2 610	22.5 (572)	89	20
10482	FB32T8/30K/8/U6/RS/G13/STD ESV	32	G13	3 000	85	20 000	2 800	2 550	22.5 (572)	88	20
10483	FB32T8/35K/8/U6/RS/G13/STD ESV	32	G13	3 500	85	20 000	2 800	2 550	22.5 (572)	88	20
10484	FB32T8/41K/8/U6/RS/G13/STD ESV	32	G13	4 100	85	20 000	2 800	2 550	22.5 (572)	88	20
10406	FB32T8/50K/8/U6/RS/G13/STD ESV	32	G13	5 000	86	20 000	2 750	2 500	22.5 (572)	86	20



\* G13 = Med Bipin

<sup>1</sup> One year warranty on lamps with less than 18 000 hours average life

<sup>2</sup> Two year warranty on lamps with more than 18 000 hours average life

# Circline & U-Bent