



These LED exit lamp kits minimize energy consumption and maintenance costs compared to their incandescent equivalent, all while evenly illuminating both sides of the sign. For greater efficiency and energy savings use the high power factor kit.

- Easy retrofit solution
- Each retrofit kit comes with multiple adapters and adjustable base

Order code	Description	Watts	Base	Volts	Colour	Shape	Average life	Power factor	Case qty
couc		(W)		(V)			(hrs)	ractor	4.7
ENS-2000									
MOL: 5 1/8	in. (130 mm) Dia.: <sup>21</sup> / <sub>32</sub> in. (42 mm)								
27115	LED/Exit/1.2W/E12/STD 2P	1.2	E12	120	Red	U shape	100 000	Normal	120
27116	LED/Exit/1.2W/E12/STD/BULK	1.2	E12	120	Red	U shape	100 000	Normal	500
59925	LED/Exit/0.9W/E12/STD	0.9	E12	120	Red	U shape	100 000	High	120

## Kit includes

- 2 lamps E12 candelabra base
- 2 adaptors for E17 intermediate base
- ► 2 adaptors for DC (BA15d) base







