



**XENON JD LAMPS** are filled with low pressure xenon gas. They provide a very bright crisp white light in a very compact lamp.

Unlike halogen filled lamps, they do not produce UV and can be handled with bare hands with no effect on lamp life. They are safe to use in open fixtures and are more tolerant to voltage fluctuations resulting in longer life.

Xenon lamps are ideal for lighting sensitive objects such as works of art.



Order code	Description	Watts (W)	Base	Volts (V)	Colour/Finish	Average life (hrs)	Initial lumens (lm)	Case qty
<b>T3 (E26)</b>								
MOL : 2 3/4 in. (70 mm)      Dia. : 1 1/2 in. (26 mm)								
15457	X40T3/F/3M/KX/120V	40	E26	50	Frost	3 000	560	50
<b>T3 (BA15d)</b>								
MOL : 2 3/32 in. (63 mm)      Dia. : 23/32 in. (18 mm)								
15439	X20T3/3M/KX/BA15D/120V	20	BA15d	120	Clear	3 000	200	50
60952	X40T3/2M/BA15D/120V/STD	40	BA15d	120	Clear	2 000	560	120
60956	X60T3/2M/BA15D/120V/STD	60	BA15d	120	Clear	2 000	960	120
<b>T3 (E11)</b>								
MOL : 2 3/4 in. (57 mm)      Dia. : 23/32 in. (18 mm)								
15440	X20T3/3M/KX/E11/120V	20	E11	120	Clear	3 000	200	50
60950	X40T3/2M/E11/120V/STD	40	E11	120	Clear	2 000	560	120
60954	X60T3/2M/E11/120V/STD	60	E11	120	Clear	2 000	960	120
<b>T3 (E12)</b>								
MOL : 2 3/16 in. (59 mm)      Dia. : 23/32 in. (18 mm)								
60948	X20T3/2M/E12/120V/STD	20	E12	120	Clear	2 000	200	120
60951	X40T3/2M/E12/120V/STD	40	E12	120	Clear	2 000	560	120
60955	X60T3/2M/E12/120V/STD	60	E12	120	Clear	2 000	960	120
<b>T3 (E12)</b>								
MOL : 1 23/32 in. (45 mm)      Dia. : 23/32 in. (18 mm)								
60949	X20T3/F/2M/E12/120V/STD	20	E12	120	Frost	2 000	200	120
60953	X40T3/F/2M/E12/120V/STD	40	E12	120	Frost	2 000	560	120
60957	X60T3/F/2M/E12/120V/STD	60	E12	120	Frost	2 000	960	120



# Xenon JD Lamps