



ES SHAPED LAMPS with a GU10 base also known as GU10 are increasingly used in decorative fixtures. Their line voltage transformer free operation is highly appreciated in general lighting.

ES lamps are also offered as specialty items with additional features.

All GU10 based lamps are fitted with a lens that filters UV rays.



ES16 (GU10)

Order code	Description	Watts (W)	Base	Volts (V)	Colour temp. (K)	Beam angle (°)	Beam spread	CBCP (cd)	Average life (hrs)	Initial lumens (lm)	Case qty
ES16 (GU10)											
MOL : 2 7/32 in. (55 mm) Dia. : 2 in. (51 mm)											
55034	H20GU10/NFL/CG/2.5M/120V/STD	20	GU10	120	2 800	25	Narrow Flood	500	2 500	120	100
55033	H35GU10/NFL/CG/2.5M/120V/STD	35	GU10	120	2 800	25	Narrow Flood	1 000	2 500	280	100
10437	H50GU10/NFL/CG/2.5M/120V/STD	50	GU10	120	2 800	25	Narrow Flood	1 400	2 500	500	100
55035	H50GU10/NFL/2M/CG/120V/ HS	50	GU10	120	2 800	25	Narrow Flood	1 400	2 000	N/A	15
10438	H50GU10/NFL/CG/3M/130V/STD	50	GU10	130	2 800	25	Narrow Flood	1 400	3 000	375	100



ES16 (GU10) Lamps