

| Order code | Description | Watts (W) | Base | Colour temp. (K) | CRI | Rated life IS (3 hrs) | Rated life IS (12 hrs) | Rated life PS/PRS (3 hrs) | Rated life PS/PRS (12 hrs) | Initial lumens (lm) | Mean lumens (lm) | Nominal length in. (mm) | Efficacy (lm/W) | Case qty |
|------------|-------------|-----------|------|------------------|-----|-----------------------|------------------------|---------------------------|----------------------------|---------------------|------------------|-------------------------|-----------------|----------|
|------------|-------------|-----------|------|------------------|-----|-----------------------|------------------------|---------------------------|----------------------------|---------------------|------------------|-------------------------|-----------------|----------|

800 series ¹

Dia. : 1 in. (26 mm)

| | | | | | | | | | | | | | | |
|-------|---------------------------------|----|------|-------|----|--------|--------|--------|--------|-------|-------|------------|----|----|
| 10014 | F17T8/30K/8/RS/G13/STD ESV | 17 | G13* | 3 000 | 85 | N/A | N/A | 24 000 | 30 000 | 1 400 | 1 330 | 24 (610) | 82 | 25 |
| 10015 | F17T8/35K/8/RS/G13/STD ESV | 17 | G13 | 3 500 | 85 | N/A | N/A | 24 000 | 30 000 | 1 400 | 1 330 | 24 (610) | 82 | 25 |
| 10002 | F17T8/41K/8/RS/G13/STD ESV | 17 | G13 | 4 100 | 85 | N/A | N/A | 24 000 | 30 000 | 1 400 | 1 330 | 24 (610) | 82 | 25 |
| 10016 | F25T8/30K/8/RS/G13/STD ESV | 25 | G13 | 3 000 | 85 | 24 000 | 30 000 | 30 000 | 36 000 | 2 150 | 2 040 | 36 (915) | 86 | 25 |
| 10912 | F25T8/35K/8/RS/G13/STD ESV | 25 | G13 | 3 500 | 85 | 24 000 | 30 000 | 30 000 | 36 000 | 2 150 | 2 040 | 36 (915) | 86 | 25 |
| 10003 | F25T8/41K/8/RS/G13/STD ESV | 25 | G13 | 4 100 | 85 | 24 000 | 30 000 | 30 000 | 36 000 | 2 150 | 2 040 | 36 (915) | 86 | 25 |
| 58635 | F25T8/830HL/ES/STD | 25 | G13 | 3 000 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 400 | 2 300 | 48 (1 220) | 96 | 25 |
| 57124 | F25T8/835HL/ES/STD | 25 | G13 | 3 500 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 400 | 2 300 | 48 (1 220) | 96 | 25 |
| 57122 | F25T8/841HL/ES/STD | 25 | G13 | 4 100 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 400 | 2 300 | 48 (1 220) | 96 | 25 |
| 56505 | F28T8/830HL/ES/STD | 28 | G13 | 3 000 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 725 | 2 560 | 48 (1 220) | 97 | 25 |
| 56506 | F28T8/835HL/ES/STD | 28 | G13 | 3 500 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 725 | 2 560 | 48 (1 220) | 97 | 25 |
| 56507 | F28T8/841HL/ES/STD | 28 | G13 | 4 100 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 725 | 2 560 | 48 (1 220) | 97 | 25 |
| 56508 | F28T8/850HL/ES/STD | 28 | G13 | 5 000 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 625 | 2 500 | 48 (1 220) | 94 | 25 |
| 56501 | F30T8/830HL/ES/STD | 30 | G13 | 3 000 | 86 | 24 000 | 30 000 | 40 000 | 42 000 | 2 850 | 2 700 | 48 (1 220) | 95 | 25 |
| 56502 | F30T8/835HL/ES/STD | 30 | G13 | 3 500 | 86 | 24 000 | 30 000 | 40 000 | 42 000 | 2 850 | 2 700 | 48 (1 220) | 95 | 25 |
| 56503 | F30T8/841HL/ES/STD | 30 | G13 | 4 100 | 86 | 24 000 | 30 000 | 40 000 | 42 000 | 2 850 | 2 700 | 48 (1 220) | 95 | 25 |
| 56504 | F30T8/850HL/ES/STD | 30 | G13 | 5 000 | 86 | 24 000 | 30 000 | 40 000 | 42 000 | 2 750 | 2 600 | 48 (1 220) | 92 | 25 |
| 51166 | F32T8/30K/8/RS/G13/STD ESV | 32 | G13 | 3 000 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 3 050 | 2 900 | 48 (1 220) | 95 | 25 |
| 51167 | F32T8/35K/8/RS/G13/STD ESV | 32 | G13 | 3 500 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 3 050 | 2 900 | 48 (1 220) | 95 | 25 |
| 51168 | F32T8/41K/8/RS/G13/STD ESV | 32 | G13 | 4 100 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 3 050 | 2 900 | 48 (1 220) | 92 | 25 |
| 59898 | F32T8/41K/8/RS/G13/STD ESV BULK | 32 | G13 | 4 100 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 3 050 | 2 900 | 48 (1 220) | 94 | 25 |
| 10004 | F32T8/50K/8/RS/G13/STD ESV | 32 | G13 | 5 000 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 950 | 2 800 | 48 (1 220) | 92 | 25 |
| 51170 | F32T8/50K/9/RS/G13/STD ESV | 32 | G13 | 5 000 | 98 | 20 000 | 24 000 | 24 000 | 30 000 | 2 100 | 2 000 | 48 (1 220) | 66 | 25 |
| 51174 | F32T8/FS/RS/G13/STD | 32 | G13 | 5 700 | 92 | 20 000 | 24 000 | 24 000 | 30 000 | 2 300 | 2 185 | 48 (1 220) | 72 | 25 |
| 51169 | F32T8/65K/8/RS/G13/STD ESV | 32 | G13 | 6 500 | 85 | 24 000 | 30 000 | 40 000 | 42 000 | 2 900 | 2 750 | 48 (1 220) | 91 | 25 |
| 10309 | F40T8/41K/8/RS/G13/STD | 40 | G13 | 4 100 | 85 | 20 000 | 24 000 | 24 000 | 30 000 | 3 700 | 3 600 | 60 (1 524) | 93 | 25 |

T8 XL31 ¹

Dia. : 1 in. (26 mm)

| | | | | | | | | | | | | | | |
|-------|---------------------|----|-----|-------|----|--------|--------|--------|--------|-------|-------|------------|----|----|
| 10914 | F32T8/830K/XL31/STD | 32 | G13 | 3 000 | 89 | 20 000 | 24 000 | 24 000 | 30 000 | 3 100 | 2 950 | 48 (1 220) | 97 | 25 |
| 10915 | F32T8/835K/XL31/STD | 32 | G13 | 3 500 | 89 | 20 000 | 24 000 | 24 000 | 30 000 | 3 100 | 2 950 | 48 (1 220) | 97 | 25 |
| 10916 | F32T8/841K/XL31/STD | 32 | G13 | 4 100 | 89 | 20 000 | 24 000 | 24 000 | 30 000 | 3 100 | 2 950 | 48 (1 220) | 97 | 25 |
| 10917 | F32T8/850K/XL31/STD | 32 | G13 | 5 000 | 89 | 20 000 | 24 000 | 24 000 | 30 000 | 3 000 | 2 850 | 48 (1 220) | 94 | 25 |

T8 Long Life ²

Dia. : 1 in. (26 mm)

| | | | | | | | | | | | | | | |
|-------|-------------------------------|----|-----|-------|----|--------|--------|--------|--------|-------|-------|------------|----|----|
| 60855 | F28T8/35K/8/RS/G13/STD ESV LL | 28 | G13 | 3 500 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 675 | 2 540 | 48 (1 220) | 96 | 25 |
| 60854 | F28T8/41K/8/RS/G13/STD ESV LL | 28 | G13 | 4 100 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 675 | 2 540 | 48 (1 220) | 96 | 25 |
| 60857 | F28T8/50K/8/RS/G13/STD ESV LL | 28 | G13 | 5 000 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 575 | 2 450 | 48 (1 220) | 92 | 25 |
| 60853 | F32T8/35K/8/RS/G13/STD ESV LL | 32 | G13 | 3 500 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 950 | 2 800 | 48 (1 220) | 92 | 25 |
| 60852 | F32T8/41K/8/RS/G13/STD ESV LL | 32 | G13 | 4 100 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 950 | 2 800 | 48 (1 220) | 92 | 25 |
| 60856 | F32T8/50K/8/RS/G13/STD ESV LL | 32 | G13 | 5 000 | 85 | 36 000 | 40 000 | 55 000 | 60 000 | 2 850 | 2 700 | 48 (1 220) | 89 | 25 |

* G13 = Med Bipin

