



JC TYPE LAMPS are low voltage capsules with pin bases.



Order code	Description	Watts (W)	Base	Volts (V)	Colour/Finish	Average life (hrs)	Initial lumens (lm)	Case qty
JC (G4)								
MOL : 1 3/16 in. (33 mm) Dia. : 15/32 in. (9 mm)								
51129	H10JC/CL/2M/G4/12V/STD	10	G4	12	Clear	2 000	130	100
51130	H20JC/CL/2M/G4/12V/STD	20	G4	12	Clear	2 000	300	100
JC (GY6.35)								
MOL : 1 23/32 in. (44 mm) Dia. : 15/32 in. (12 mm)								
50902	H50JC/CL/4M/GY6.35/12V/STD	50	GY6.35	12	Clear	4 000	900	100
JC (GY6.35)								
MOL : 2 1/4 in. (57 mm) Dia. : 15/32 in. (12 mm)								
22121	200T4/CL/32V/GY9.5/STD 1945	200	GY9.5	32	Clear	200	4 500	100

JD TYPE LAMPS are tubular shaped and run on line voltage. JD halogen lamps can have E26, BA15d, E11, E12, E14 and G9 bases.



Order code	Description	Watts (W)	Base	Volts (V)	Colour/Finish	Average life (hrs)	Initial lumens (lm)	Case qty
T3 (BA15d)								
MOL : 2 7/32 in. (56 mm) Dia. : 19/32 in. (15 mm)								
50881	H75T3/CL/2M/BA15D/130V/STD	75	BA15d	130	Clear	2 000	1 120	120
50950	H100T3/CL/2M/BA15D/130V/STD	100	BA15d	130	Clear	2 000	1 600	50
50883	H150T3/CL/2M/BA15D/130V/STD	150	BA15d	130	Clear	2 000	3 000	120
50885	H250T3/CL/2M/BA15D/130V/STD	250	BA15d	130	Clear	2 000	4 800	50
T3 (E11)								
MOL : 2 15/32 in. (63 mm) Dia. : 23/32 in. (18 mm)								
55028	H50T3/CL/2M/E11/130V/STD	50	E11	130	Clear	2 000	1 120	120
50880	H75T3/CL/2M/E11/130V/STD	75	E11	130	Clear	2 000	1 350	120
50882	H100T3/CL/2M/E11/130V/STD	100	E11	130	Clear	2 000	1 800	120
50951	H150T3/CL/2M/E11/130V/STD	150	E11	130	Clear	2 000	3 000	120
50884	H250T3/CL/2M/E11/130V/STD	250	E11	130	Clear	2 000	4 800	50



JC & JD Lamps